

Material 32036.294
 Material description Buffer solution pH 6
 Grade

Additional information

Characteristics	Specifications
pH (20°C) (tolerance ± 0.02)	5.98 --> 6.02
pH laboratory uncertainty	± 0.010 (k=1)
pH homogeneity uncertainty	± 0.003 (k=1)
pH stability uncertainty	± 0.005 (k=1)
pH expanded, combined uncertainty	± 0.03 (k=2; 95 %)

Signature

This document has been produced electronically and is valid without a signature.

Anja Vanhalle, Head of Laboratory - Haasrode
 VWR International bvba; Geldenaaksebaan 464; BE-3001
 Leuven; Belgium



Additional information

pH-Method: pH value is analyzed with a glass electrode after 4-point calibration following the validated standard procedure of ISO/IEC 17025 accreditation. The expanded uncertainty relevant for the user contains contributions of bottle to bottle variation (inhomogeneity), stability over time and laboratory measurement uncertainties as shown above and using a coverage factor k=2 for a 95 % coverage probability.

Preparation: This reference material is prepared gravimetrically from citric acid, sodium hydroxide and high purity water.

Accreditation: VWR International BVBA is accredited as calibration laboratory according to ISO/IEC 17025. The batch homogeneity has been proven by analyzing minimum 6 samples distributed over the entire production process. The expiry date is not part of the accreditation.

The pH of this buffer solution is traceable to and verified against primary Standard Reference Materials (SRM) from National Institute of Standards and Technology (NIST): SRM 188 and SRM 187e.

Store at +2°C to +25°C tightly closed in the original container under nitrogen.