Product Specification

Material	32039.374
Material description	Buffer solution pH 9
Grade	

Additional information

Characteristics	Specifications
pH (20°C) (tolerance ± 0.02)	8.98 --> 9.02
pH laboratory uncertainty	± 0.010 (k=1)
pH homogeneity uncertainty	± 0.003 (k=1)
pH stability uncertainty	± 0.020 (k=1)
pH expanded, combined uncertainty	± 0.05 (k=2; 95 %)

Signature

This document has been produced electronically and is valid without a signature.

Anja Vanhalle, Head of Laboratory - Haasrode
VWR International bvba; Geldenaaksebaan 464; BE-3001 Leuven; Belgium

ISO/IEC 17025
CALIBRATION ACCREDITATION
BELAC
NBN EN ISO/IEC 17025:2005
N°: 542-CAL
VWR International BVBA
Quality Control Laboratory
Geldenaaksebaan 464
BE-3001 Leuven, Belgium
Coverage available on: www.belac.be

Additional information

pH-Method: pH value is analyzed with a glass electrode after 4-point calibration following the validated standard procedure of ISO/IEC 17025 accreditation. The expanded uncertainty relevant for the user contains contributions of bottle to bottle variation (inhomogeneity), stability over time and laboratory measurement uncertainties as shown above and using a coverage factor k=2 for a 95 % coverage probability.

Preparation: This reference material is prepared gravimetrically from boric acid, potassium chloride and high purity water.

Accreditation: VWR International BVBA is accredited as calibration laboratory according to ISO/IEC 17025. The batch homogeneity has been proven by analyzing minimum 6 samples distibuted over the entire production process. The expiry date is not part of the accreditation.

The pH of this buffer solution is traceable to and verified against primary Standard Reference Materials (SRM) from National Institute of Standards and Technology (NIST): SRM 186 I + II g and SRM 191d I + II.

Store at +2°C to +25°C tightly closed in the original container under nitrogen.

For Professional use in Laboratory or Manufacturing. Not for use as an Active Pharmaceutical Ingredient or Food or Animal Feed. Suitability and intended use of the product remains the responsibility of the user.